



NCN101A

**MCB 1P 10kA/15kA C-1A 1M**

**Technical characteristics**

**Electric current**

Rated current	1 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity $I_{cu}$ under 230 V AC IEC 60947-2	15 kA
Rated current -25°C	1.34 A
Rated current at -20°C	1.32 A
Rated current -15°C	1.29 A
Rated current -10°C	1.26 A
Rated current -5°C	1.23 A
Rated current at 0°C	1.20 A
Rated current 5°C	1.17 A
Rated current 10°C	1.14 A
Rated current 15°C	1.10 A
Rated current at 20°C	1.07 A
Rated current 25°C	1.04 A
Rated current 30°C	1 A
Rated current 35°C	0.96 A
Rated current at 40°C	0.92 A
Rated current at 45°C	0.88 A
Rated current at 50°C	0.84 A
Rated current 55°C	0.80 A
Rated current 60°C	0.75 A
Rated current 65°C	0.70 A
Rated current 70°C	0.64 A

**Architecture**

Type of pole	1P
Curve	C

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity $I_{cn}$ AC according to IEC 60898-1	10 kA
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

<b>Voltage</b>	
Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6,000 V
<b>Frequency</b>	
Frequency	50 - 60 Hz
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
<b>Installation, mounting</b>	
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C
<b>Power</b>	
Total power loss under IN	0.13 W
<b>Endurance</b>	
Electric endurance in number of cycles	4,000
Number of mechanical operations	20,000
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	17.50 mm
Depth	70 mm