



NCN225A

**MCB 2P 10kA/15kA C-25A 2M**

**Technical characteristics**

**Architecture**

Neutral position	without neutral
Number of poles	2 P
Curve	C

**Main electrical features**

Rated operational voltage Ue	400 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated service breaking capacity Ics AC according IEC 60898-1	7.5 kA
Rated service breaking capacity Ics under 400V AC according IEC 60947-2	7.5 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	10 kA

**Electric current / temperature**

Rating current 30°C	25 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	7.2 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Standards**

Standard text	EN 60898-1 ; IEC 60947-2
European directive WEEE	concerned

**Safety**

---

Protection index IP

IP20

**Use conditions**

---

Operating temperature

-25...70 °C