



HND630H

Moulded Case Circuit Breaker h630 3P 50kA 630A LSI

Technical Characteristics

Number of poles	3 P
Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz
Rated current	630 A
Rated insulation voltage	800 V
Total power loss under IN	120 W
Number of mechanical operations	4000
Number of modules	8
Interlockable	No
Tightening torque	22Nm
Connection cross-sect. flexible conductor	35 / 240mm ²
Connection cross-sect. rigid cable	35 / 240mm ²
Type of connection	Terminal
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	No
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X