



HND631H

Moulded Case Circuit Breaker h630 4P 50kA 630A LSI

Technical characteristics

Architecture

Number of poles 4 P

Main electrical features

Rated operational voltage Ue 220 / 690 V

Frequency 50/60 Hz

Voltage

Rated insulation voltage 800 V

Rated impulse withstand voltage 8 kV

Power

Total power loss under I_N 120 W

Endurance

Electric endurance in number of cycles 1000

Number of mechanical operations 4000

Connection

Connection cross-sect. rigid cable 35 / 240mm²

Type of connection Terminal

Equipment

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 0

Standards

Standard text IEC 60947-2

European directive WEEE concerned

Use conditions

Operating temperature -25...70 °C