



HND631H

**Moulded Case Circuit Breaker h630 4P 50kA 630A LSI**

**Technical characteristics**

**Architecture**

Number of poles 4 P

**Main electrical features**

Rated operational voltage Ue 220 / 690 V

Frequency 50/60 Hz

**Voltage**

Rated insulation voltage 800 V

Rated impulse withstand voltage 8 kV

**Power**

Total power loss under IN 120 W

**Endurance**

Electric endurance in number of cycles 1000

Number of mechanical operations 4000

**Connection**

Connection cross-sect. rigid cable 35 / 240mm<sup>2</sup>

Type of connection Terminal

**Equipment**

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 0

**Standards**

Standard text IEC 60947-2

European directive WEEE concerned

**Use conditions**

Operating temperature -25...70 °C