



HNF980H

Moulded Case Circuit Breaker h1600 3P 50kA 1250A LSI

Technical Characteristics

Number of poles	3 P
Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz
Rated current	1250 A
Rated insulation voltage	800 V
Total power loss under IN	187.5 W
Number of mechanical operations	4000
Number of modules	12
Tightening torque	65Nm
Connection cross-sect. flexible conductor	3x240mm ²
Connection cross-sect. rigid cable	3x240mm ²
Type of connection	Terminal
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X