



HNG125U

Moulded Case Circuit Breaker h250 3P 50kA 125A TM

Technical characteristics

Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA

Architecture

Number of poles	3
-----------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	800 V

Functions

Trip unit	TM A/A
-----------	--------

Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

Power

Total power loss under IN	29.60 W
---------------------------	---------

Endurance

Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²
Connector/plug type	Terminal

Installation, mounting

Nominal tightening torque	12 - 12 Nm
---------------------------	------------

Mounting-/Connection Position	Front
Settings	
Thermal protection knob setting xIN	0.63, 0.8, 1
Adjustment range short-term delayed short-circuit release	0 - 0 A