



HR520

## EARTH LEAKAGE RELAY 0.03-10A TIME DELAY 50% LED

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue 230 V

#### Voltage

Max operating voltage 276 V

#### Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A / 10 A

#### Power

Power consumed 5 VA

#### Installation, mounting

Tightening torque 1,7Nm

#### Connection

Connection cross-sect. flexible conductor 1 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 4mm<sup>2</sup>

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP30

Residual current type A

#### Use conditions

Operating temperature -10...55 °C