



HR520

## EARTH LEAKAGE RELAY 0.03-10A TIME DELAY 50% LED

### Technical characteristics

#### Electric current

Rated residual operating current $I_{dn}$	30 mA, 100 mA, 300 mA, 500 mA, 1000 mA, 3000 mA, 10000 mA
Toroid's: Allowed overload	30 kA/100 ms

#### Equipment

With earth leakage toroid	Yes
---------------------------	-----

#### Safety

Residual current type	A
-----------------------	---

#### Dimensions

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------