



L50600



## Fuse carrier 1P+N 32A 400V L38 1M

### Technical characteristics

#### Dimensions

Height	77 mm
Width	17.50 mm
Depth	75 mm

#### Architecture

Number of poles	2
-----------------	---

#### Electric current

Rated current	32 A
Rated current of fuse cartridge	2 A, 4 A, 6 A, 8 A, 10 A, 12 A, 16 A, 20 A, 25 A, 32 A

#### Capacity

Number of modules	1
-------------------	---

#### Internal use only

Number of half modules of 17,5 mm	2
-----------------------------------	---

#### Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

#### Installation, mounting

Nominal tightening torque	1.80 - 1.80 Nm
Mounting on	DIN rail

#### Power

Total power loss under IN	1.50 W
---------------------------	--------

#### Voltage

Type voltage supply	AC
---------------------	----

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Connection

Cross-section of input and output with screws, for flexible conductors	10 - 10 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	16 - 16 mm <sup>2</sup>

#### Fuse

Fuse size	10 x 38
-----------	---------

