



LS701



Fuse carrier 1P 125A 690V L58 accessoriability 2M

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Controls and indicators

| | |
|----------------|----|
| Indicator lamp | no |
|----------------|----|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 690 V |
| Frequency | 50 Hz |

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 96 mm |
| Height of installed product | 125 mm |
| Width of installed product | 35 mm |

Power

| | |
|---------------------------|---------|
| Total power loss under IN | 12.84 W |
|---------------------------|---------|

Endurance

| | |
|---------------------------------|------|
| Number of mechanical operations | 5000 |
|---------------------------------|------|

Cover, door

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 3,6Nm |
|-------------------|-------|

Connection

| | |
|---|-------------|
| Connection cross-sect. flexible conductor | 35 mm² max. |
| Connection cross-sect. rigid cable | 50mm² max. |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...40 °C |
|-----------------------|------------|