



MB132A

## MCB 1P 6kA B-32A 1M

### Technical characteristics

#### Electric current

Rated current	32 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	37.50 A
Rated current -10°C	37 A
Rated current -5°C	36.40 A
Rated current at 0°C	35.80 A
Rated current 5°C	35.20 A
Rated current 10°C	34.60 A
Rated current 15°C	33.90 A
Rated current at 20°C	33.30 A
Rated current 25°C	32.70 A
Rated current 30°C	32 A
Rated current 35°C	31.30 A
Rated current at 40°C	30.60 A
Rated current at 45°C	29.90 A
Rated current at 50°C	29.20 A
Rated current 55°C	28.50 A
Rated current 60°C	27.70 A
Rated current 65°C	27 A
Rated current 70°C	26.30 A

#### Architecture

Type of pole	1P
Curve	B

#### Capacity

Number of modules	1
-------------------	---

#### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

#### Main electrical attributes

### Voltage

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4,000 V

### Frequency

Frequency	50 - 60 Hz
-----------	------------

### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	4.40 W
---------------------------	--------

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	17.50 mm
Depth	70 mm