



MBN106A

**MCB 1P 6kA B-6A 1M**

**Technical characteristics**

**Architecture**

Number of poles	1 P
Curve	B

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current 30°C	6 A
---------------------	-----

**Dimensions**

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	1.3 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Installation, mounting**

Tightening torque	2,8Nm
-------------------	-------

**Connection**

Type of connection	with screw
--------------------	------------

**Standards**

Standard text	EN 60898-1
---------------	------------

**Safety**

---

Protection index IP

IP20

**Use conditions**

---

Operating temperature

-25...70 °C