



MLN710A

## MCB 1P+N 6kA C-10A 1M

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	2 P
Type of pole	1P+N
Curve	C

#### Main electrical features

Rated operational voltage U <sub>e</sub>	230 / 240 V
Frequency	50/60 Hz
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated service breaking capacity I <sub>cs</sub> AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	6 kA

#### Electric current / temperature

Rating current 30°C	10 A
---------------------	------

#### Dimensions

Depth of installed product	70 mm
Height of installed product	84.7 mm
Width of installed product	17.5 mm

#### Power

Total power loss under I <sub>N</sub>	2.6 W
---------------------------------------	-------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	20000

#### Installation, mounting

Tightening torque	1,9Nm
-------------------	-------

#### Standards

Standard text	EN 60898-1
---------------	------------

European directive WEEE

concerned

### Safety

Protection index IP

IP20

### Use conditions

Operating temperature

-25...70 °C