



MLN732A

MCB 1P+N 6kA C-32A 1M

Technical Characteristics

Neutral position	left
Number of poles	2 P
Type of pole	1P+N
Curve	C
Rated operational voltage Ue	230 / 240 V
Frequency	50/60 Hz
Rated current	32 A
Type of supply voltage	AC
Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V
Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rating current 30°C	32 A
Depth of installed product	70 mm
Height of installed product	84.7 mm
Width of installed product	17.5 mm
Total power loss under IN	6.1 W
Electric endurance in number of cycles	1000
Number of mechanical operations	20000
Number of modules	1
Tightening torque	1,9Nm
Type of connection	with screw
Standard text	EN 60898-1
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-25...70 °C