



NBN210A

MCB 2P 10kA/15kA B-10A 2M

Technical characteristics

Electric current

| | |
|---|---------|
| Rated current | 10 A |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 30 kA |
| Rated current -25°C | 12.86 A |
| Rated current at -20°C | 12.63 A |
| Rated current -15°C | 12.39 A |
| Rated current -10°C | 12.15 A |
| Rated current -5°C | 11.90 A |
| Rated current at 0°C | 11.65 A |
| Rated current 5°C | 11.39 A |
| Rated current 10°C | 11.13 A |
| Rated current 15°C | 10.86 A |
| Rated current at 20°C | 10.58 A |
| Rated current 25°C | 10.29 A |
| Rated current 30°C | 10 A |
| Rated current 35°C | 9.70 A |
| Rated current at 40°C | 9.39 A |
| Rated current at 45°C | 9.06 A |
| Rated current at 50°C | 8.73 A |
| Rated current 55°C | 8.38 A |
| Rated current 60°C | 8.02 A |
| Rated current 65°C | 7.64 A |
| Rated current 70°C | 7.24 A |

Architecture

| | |
|--------------|----|
| Type of pole | 2P |
| Curve | B |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |

| | |
|---|------------------------|
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |
| Main electrical attributes | |
| Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1 | 10 kA |
| Voltage | |
| Rated operational voltage U _e | 400 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage U _i | 500 V |
| Rated impulse withstand voltage U _{imp} | 6,000 V |
| Frequency | |
| Frequency | 50 - 60 Hz |
| Connection | |
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |
| Safety | |
| Ingress Protection (IP) class | IP20 |
| Use conditions | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Operating temperature | -25 - 70 °C |
| Power | |
| Total power loss under I _N | 4.13 W |
| Endurance | |
| Electric endurance in number of cycles | 4,000 |
| Number of mechanical operations | 20,000 |
| Connectivity | |
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |
| Dimensions | |
| Height | 83 mm |
| Width | 35 mm |
| Depth | 70 mm |