



NBN316A

## MCB 3P 10kA/15kA B-16A 3M

### Technical characteristics

#### Electric current

Rated current	16 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	15 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated current -25°C	20.27 A
Rated current at -20°C	19.92 A
Rated current -15°C	19.56 A
Rated current -10°C	19.20 A
Rated current -5°C	18.83 A
Rated current at 0°C	18.45 A
Rated current 5°C	18.07 A
Rated current 10°C	17.67 A
Rated current 15°C	17.27 A
Rated current at 20°C	16.86 A
Rated current 25°C	16.43 A
Rated current 30°C	16 A
Rated current 35°C	15.48 A
Rated current at 40°C	14.94 A
Rated current at 45°C	14.38 A
Rated current at 50°C	13.80 A
Rated current 55°C	13.19 A
Rated current 60°C	12.56 A
Rated current 65°C	11.89 A
Rated current 70°C	11.18 A

#### Architecture

Type of pole	3P
Curve	B

#### Capacity

Number of modules	3
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

<b>Voltage</b>	
Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6,000 V
<b>Frequency</b>	
Frequency	50 - 60 Hz
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1 - 35 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for massive conductors	1 - 35 mm²
<b>Installation, mounting</b>	
Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I²t	3
Operating temperature	-25 - 70 °C
<b>Power</b>	
Total power loss under IN	8.27 W
<b>Endurance</b>	
Electric endurance in number of cycles	4,000
Number of mechanical operations	20,000
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	52.50 mm
Depth	70 mm