



SBB132

**1-pole, 32A Modular Switch with Indicator Light**

**Technical characteristics**

**Architecture**

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	1.6 W
---------------------------	-------

**Endurance**

Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

**Lighting control**

Type of lamp	LED
--------------	-----

**Installation, mounting**

Tightening torque	1,8Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 16mm <sup>2</sup>
Type of connection	with screw

**Standards**

Standard text	IEC 60947-3 ; IEC/EN 60669-1
---------------	------------------------------

**Use conditions**

Operating temperature	-20...50 °C
-----------------------	-------------