



SBB225

2-pole, 25A Modular Switch with Indicator Light

Technical characteristics

Architecture

Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	1.9 W
---------------------------	-------

Endurance

Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

Lighting control

Type of lamp	LED
--------------	-----

Standards

Standard text	IEC 60947-3 ; IEC/EN 60669-1
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------