



SBN125

## 1-pole, 25A Modular Switch

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Power

Total power loss under IN	0.9 W
---------------------------	-------

#### Endurance

Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

#### Standards

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
European directive WEEE	concerned

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------