



NCN306A



**MCB 3P 10kA/15kA C-6A 3M**

**Technical characteristics**

**Architecture**

|                  |                 |
|------------------|-----------------|
| Neutral position | without neutral |
| Number of poles  | 3 P             |
| Type of pole     | 3 P             |
| Curve            | C               |

**Main electrical features**

|                                 |       |
|---------------------------------|-------|
| Rated operational voltage $U_e$ | 400 V |
| Type of supply voltage          | AC    |

**Voltage**

|                                 |        |
|---------------------------------|--------|
| Rated insulation voltage        | 500 V  |
| Rated impulse withstand voltage | 6000 V |

**Electric current**

|   |        |
|---|--------|
| Rated service breaking capacity $I_{cs}$ AC according IEC 60898-1                 | 7.5 kA |
| Rated service breaking capacity $I_{cs}$ under 400V AC according IEC 60947-2      | 7.5 kA |
| Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1 | 10 kA  |

**Electric current / temperature**

|                     |     |
|---------------------|-----|
| Rating current 30°C | 6 A |
|---------------------|-----|

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 70 mm   |
| Height of installed product | 83 mm   |
| Width of installed product  | 52.5 mm |

**Power**

|                              |        |
|------------------------------|--------|
| Total power loss under $I_N$ | 4.06 W |
|------------------------------|--------|

**Endurance**

|  |       |
|--|-------|
| Electric endurance in number of cycles | 4000  |
| Number of mechanical operations        | 20000 |

**Installation, mounting**

|                   |       |
|-------------------|-------|
| Tightening torque | 2,8Nm |
|-------------------|-------|

**Equipment**

|                     |     |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

**Standards**

---

Standard text

EN 60898-1 ; IEC 60947-2

**Use conditions**

---

Operating temperature

-25...70 °C