



SFT225

2-pole, 25A Centre Off Modular Changeover Switch with Top Common Point

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under IN	1.8 W
---------------------------	-------

Endurance

Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

Installation, mounting

Tightening torque	1,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1,5 / 16mm ²
Type of connection	with screw

Standards

Standard text	IEC 60947-3 ; IEC/EN 60669-1
---------------	------------------------------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------