



NCN403A

MCB 4P 10kA/15kA C-3A 4M

Technical characteristics

Electric current

| | |
|---|--------|
| Rated current | 3 A |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 15 kA |
| Rated current -25°C | 3.57 A |
| Rated current at -20°C | 3.52 A |
| Rated current -15°C | 3.47 A |
| Rated current -10°C | 3.42 A |
| Rated current -5°C | 3.37 A |
| Rated current at 0°C | 3.32 A |
| Rated current 5°C | 3.27 A |
| Rated current 10°C | 3.22 A |
| Rated current 15°C | 3.17 A |
| Rated current at 20°C | 3.11 A |
| Rated current 25°C | 3.06 A |
| Rated current 30°C | 3 A |
| Rated current 35°C | 2.93 A |
| Rated current at 40°C | 2.85 A |
| Rated current at 45°C | 2.77 A |
| Rated current at 50°C | 2.69 A |
| Rated current 55°C | 2.60 A |
| Rated current 60°C | 2.52 A |
| Rated current 65°C | 2.43 A |
| Rated current 70°C | 2.33 A |

Architecture

| | |
|--------------|----|
| Type of pole | 4P |
| Curve | C |

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |

| | |
|---|------------------------|
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |
| Main electrical attributes | |
| Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1 | 10 kA |
| Voltage | |
| Rated operational voltage U _e | 400 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage U _i | 500 V |
| Rated impulse withstand voltage U _{imp} | 6,000 V |
| Frequency | |
| Frequency | 50 - 60 Hz |
| Connection | |
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |
| Safety | |
| Ingress Protection (IP) class | IP20 |
| Use conditions | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Operating temperature | -25 - 70 °C |
| Power | |
| Total power loss under I _N | 8.86 W |
| Endurance | |
| Electric endurance in number of cycles | 4,000 |
| Number of mechanical operations | 20,000 |
| Connectivity | |
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |
| Dimensions | |
| Height | 83 mm |
| Width | 70 mm |
| Depth | 70 mm |