



SM100

Analogue ammeter 0-100A indirect reading

Technical characteristics

Main electrical features

Frequency	45/65 Hz
-----------	----------

Voltage

Rated insulation voltage	2000 V
--------------------------	--------

Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	1.1 VA
Total power loss under IN	1.1 W

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------