



SPA001N

Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV

Technical characteristics

Main electrical features

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 100 kA

Dimensions

Depth of installed product 52.3 mm

Height of installed product 46.4 mm

Width of installed product 35.5 mm

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -40...80 °C