



SPA081

Cartridge L-N/PEN Uc 350V Iimp 25kA Up 1.5kV for SPA80X

Technical characteristics

Electric current

Max. discharge (I _{max}) L-N(PEN)/ N-PE	50 kA
Lightning impulse current I _{imp} (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	25 kA

Network configuration

Network type	TN, TT
--------------	--------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Capacity

Number of modules	2
-------------------	---

Voltage

Voltage protection level U _p according to IEC 61643-1	1.50 kV
Continuous operating voltage U _c according to IEC 61643-1	350 V

Architecture

Number of poles	1
-----------------	---

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Dimensions

Height	44.8 mm
Width	35.50 mm
Depth	56.1 mm

Controls and indicators

With indicator lamp	Yes
---------------------	-----

Standards

Requirement class IEC 61643	T1, T2
-----------------------------	--------