



SRA02505

**Bar/Cable-through Current Transformer BG 113 250/5A 2,5VA Class 1**

**Technical characteristics**

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Voltage**

Rated insulation voltage	3 kV
--------------------------	------

**Dimensions**

Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	49.5 mm
Height of opening	20 mm

**Power**

Total power loss under IN	2.6 W
---------------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Operating temperature	-40...40 °C
-----------------------	-------------