



SRA02505

### Bar/Cable-through Current Transformer BG 113 250/5A 2,5VA Class 1

#### Technical characteristics

##### Main electrical features

Frequency	50/60 Hz
-----------	----------

##### Voltage

Rated insulation voltage	3 kV
--------------------------	------

##### Dimensions

Depth of installed product	30 mm
----------------------------	-------

Height of installed product	70 mm
-----------------------------	-------

Width of installed product	49.5 mm
----------------------------	---------

Height of opening	20 mm
-------------------	-------

##### Power

Total power loss under IN	2.6 W
---------------------------	-------

##### Connection

Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
---	------------------------

Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>
------------------------------------	------------------------

Type of connection	screw
--------------------	-------

##### Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------