



SRC04005

### Bar/Cable-through Current Transformer BG 113 400/5A 5VA Class 1

#### Technical characteristics

##### Main electrical features

Frequency 50/60 Hz

##### Voltage

Rated insulation voltage 3 kV

##### Dimensions

Depth of installed product 30 mm

Height of installed product 70 mm

Width of installed product 50 mm

Height of opening 20 mm

##### Power

Total power loss under IN 3.6 W

##### Connection

Type of connection screw

##### Standards

European directive WEEE concerned

##### Use conditions

Operating temperature -40...40 °C