



SRE20005

Bar/Cable-through Current Transformer BG 814 2000/5A 15VA Class 1

Technical characteristics

Specific identification attributes for Protection

Filter Type product Plug-in current transformer

Functions

Accuracy class 1

Power

Power 15 VA

Total power loss under IN 17.50 W

Dimensions

Diameter of opening 60 mm

Height 122 mm

Width 100 mm

Depth 40 mm

Height of opening 60 mm

Width of opening 81 mm

Connectivity

Type of connection Screw terminal

Frequency

Frequency 50 - 60 Hz

Voltage

Rated insulation voltage Ui 3,000 V

Use conditions

Operating temperature -40 - 40 °C

Storage/transport temperature -40 - 40 °C

Connection

Cross-section flexible conductor 1.5 - 6 mm²

Cross-section rigid conductor 1.5 - 6 mm²

Safety

Ingress Protection (IP) class IP10

Electric current

Max. intensity of primary 2,000 A

Max. intensity of secondary 5 A

