



SRI03005

**Bar/Cable-through Current Transformer BG 413 300/5A 5VA Class 1**

**Technical characteristics**

**Main electrical features**

|           |          |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

**Voltage**

|                          |      |
|--------------------------|------|
| Rated insulation voltage | 3 kV |
|--------------------------|------|

**Dimensions**

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 30 mm |
| Height of installed product | 78 mm |
| Width of installed product  | 60 mm |
| Height of opening           | 28 mm |

**Power**

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 3 W |
|---------------------------|-----|

**Connection**

|                    |       |
|--------------------|-------|
| Type of connection | screw |
|--------------------|-------|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP10 |
|---------------------|------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -40...40 °C |
|-----------------------|-------------|