



TE370

IP20

3Ph Kwhmeter via CT with KNX output

Technical characteristics

Architecture

Bus system KNX

Connectivity

Bus system radio frequent No

Main electrical features

Frequency 50/60 Hz

Power

Total power loss under IN 2 W

Connection

Type of connection direct

Terminal with connecting terminal for tariff input (HT/NT) ;
with 3-phase mains connection terminal ; 3
connecting terminals for current transformers

Type of connection with screw terminals

Equipment

Type of counter other

Use conditions

Operating temperature -10...55 °C