



TRM691E



IP20

Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio

Technical characteristics

Functions

| | |
|----------|-------------------------------------|
| Function | reset function (to factory setting) |
|----------|-------------------------------------|

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Connectivity

| | |
|---------------------------|-----|
| Bus system radio frequent | Yes |
|---------------------------|-----|

Fuse

| | |
|------|--|
| Fuse | short-circuit and overload proof (electronic fuse) |
|------|--|

Dimensions

| | |
|--------|-------|
| Height | 38 mm |
|--------|-------|

Power

| | |
|-------------------------|------------|
| Incandescent bulb power | 10 / 200 W |
|-------------------------|------------|

Incandescent bulbs control

| | |
|------------------------------------|-------|
| Max. power with incandescent lamps | 200 W |
|------------------------------------|-------|

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,5 / 1,5mm ² |
| Connection cross-sect. rigid cable | 0,5 / 2,5mm ² |
| Type of load | universal |
| Number of contacts | 1 |

Equipment

| | |
|-------------------|---|
| Dimming principle | phase cut-on or cut-off according to load type, self-learning |
|-------------------|---|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15...45 °C |
|-----------------------|-------------|