



TXA112

IP20

**Power supply 30V DC 640 mA**

**Technical characteristics**

**Architecture**

Bus system EIB

**Main electrical features**

Frequency 50/60 Hz

**Fuse**

Fuse with electronic short-circuit and overload protection

**Dimensions**

Depth of installed product 64 mm

Height of installed product 90 mm

Width of installed product 72 mm

**Power**

Total power loss under IN 15 W

**Materials**

RAL colour RAL 7035 - Light grey

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of connection quick connect

Type of connection with QuickConnect plug-in terminals

**Use conditions**

Operating temperature -5...45 °C