



TXA112



**Power supply 30V DC 640 mA**

**Technical characteristics**

**Architecture**

Fixing mode Din-Rail

**Main electrical features**

Frequency 50/60 Hz

**Dimensions**

Depth of installed product 64 mm

Height of installed product 90 mm

Width of installed product 72 mm

**Power**

Total power loss under IN 15 W

**Materials**

Colour stone grey

RAL colour RAL 7035 - Light grey

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...45 °C