



TXA207C

Output 10 -fold 16A

Technical characteristics

Architecture

| | |
|-------------|----------|
| Bus system | EIB |
| Fixing mode | Din-Rail |

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Connectivity

| | |
|---------------------------|----|
| Bus system radio frequent | No |
|---------------------------|----|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 230 V |
|------------------------------|-------|

Power

| | |
|-------------------------------------|--------|
| Max. power with electronic transfo. | 1200 W |
| Total power loss under IN | 15 W |

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

Fluorescent bulbs control

| | |
|--|-----------|
| Max. power fluo. duo lamp comp. series | 20 x 36 W |
|--|-----------|

Incandescent bulbs control

| | |
|------------------------------------|--------|
| Max. power with incandescent lamps | 2300 W |
|------------------------------------|--------|

Connection

| | |
|---|---------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,75 / 2.5mm ² |
| Type of connection | quick connect |
| Type of contacts | 10NO |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 0...45 °C |
|-----------------------|-----------|