



TYA661BN



Dimmer 1 channel 600W

Technical characteristics

Functions

Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
----------	--

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Fuse

Fuse	short-circuit proof and overload proof (display using LEDs) ; overheating protection (display using LEDs)
------	---

Power

Incandescent bulb power	600 W
Total power loss under IN	320 mW
Power dissipation per coil	180 mW

Power supply

Supply voltage	230 V AC
----------------	----------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of load	universal
Type of connection	quick connect
Type of connection	with QuickConnect plug-in terminals

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning ; minimum/maximum dimming values per channel settable on device
-------------------	---

Safety

Protection	with overheating, overload and short-circuit protection
------------	---

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------