


TYA664AN



DIMMER 4 CHANNELS 300W WITH PARALLELIZATION

Technical characteristics

Architecture

Fixing mode	REG
-------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Fuse

Fuse	overheating protection (display using LEDs)
------	---

Power

Incandescent bulb power	5 / 300 W
Total power loss under IN	0.35 W
Power dissipation per coil	1 W

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Materials

Colour	RAL 7035
--------	----------

Incandescent bulbs control

Max. power with incandescent lamps	300 W
------------------------------------	-------

Connection

Type of load	universal
--------------	-----------

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------