


TYA664AN



DIMMER 4 CHANNELS 300W WITH PARALLELIZATION

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Frequency 50/60 Hz

Fuse

Fuse overheating protection (display using LEDs)

Power

Incandescent bulb power 5 / 300 W

Total power loss under IN 0.35 W

Power dissipation per coil 1 W

Power supply

Supply voltage 230 V +10% / -15%

Materials

Colour RAL 7035

Incandescent bulbs control

Max. power with incandescent lamps 300 W

Connection

Type of load universal

Equipment

Dimming principle phase cut-on or cut-off according to load type, self-learning

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C