



VML12020

Consumer unit, Design 10, dual row, 20+20 way, 100A switch disconnector incomer

Technical characteristics

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	No

Capacity

Number of modules	40
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	100 mm
Height	485 mm
Width	476 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

Number of rows	2
Number of rails	2

Extension possible	No
--------------------	----

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC