



VML24AH

2 Way Garage Consumer Unit 40A 30mA Type A RCCB

Technical characteristics

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	Yes
Overvoltage protection	No

Capacity

Number of modules	4
-------------------	---

Electric current

Rated current	40 A
---------------	------

Dimensions

Depth	98.20 mm
Height	245 mm
Width	225 mm
Number of width units	2

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	1
-----------------------------	---

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------