



VML402AH

## 2 Way 40A 30mA Type A RCCB Incomer

### Technical characteristics

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Architecture

Number of poles	2
-----------------	---

#### Functions

Has protection main switch	Yes
----------------------------	-----

#### Capacity

Number of modules	2
-------------------	---

#### Electric current

Rated current	40 A
---------------	------

#### Dimensions

Depth	98.20 mm
Height	245 mm
Width	154 mm

#### Cover, door

Interlockable	No
Door/cover is transparent	No

#### Materials

Colour	Pure white
Material	Steel

#### Connection

Number of accessible phases	2
-----------------------------	---

#### Scope of delivery

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	2

#### Equipment

Number of rows	1
----------------	---

#### Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------