



VML60810CU

Dual Row Hi Integrity 8+10 Way 63A Switch 2*63A 30mA RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	227 mm
Number of modules	18
Interlockable	No
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC
