



VML61214CU

**Dual Row Hi Integrity 12+14 Way 63A Switch 2\*63A 30mA RCCB**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Dimensions**

Depth of installed product 83 mm

Height of installed product 246 mm

Width of installed product 370 mm

**Cover, door**

Interlockable No

**Materials**

Material Steel

**Equipment**

Number of rows 2

Can be accessorized Yes

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP2XC