



WFCC50NBSW

45A Cooker Control Unit Brushed Steel White Insert

Technical characteristics

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Rated current | 45 A |

Dimensions

| | |
|--------|---------|
| Depth | 39.6 mm |
| Height | 86 mm |
| Width | 146 mm |

Cover, door

| | |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

Materials

| | |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

Connection

| | |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

Cable

| | |
|--------|------------------------------|
| Wiring | with double earth connection |
|--------|------------------------------|

Scope of delivery

| | |
|-----------|-----------------------------------|
| Component | with 2 fixing screws M3.5 x 20 mm |
|-----------|-----------------------------------|

Safety

| | |
|------------|-----------------------------|
| Protection | to protect downstream loads |
|------------|-----------------------------|

Use conditions

| | |
|--------|--------------|
| Insert | insert white |
|--------|--------------|