



SBN380

### 3-pole, 80A Modular Switch

#### Technical characteristics

##### Architecture

Number of poles	3
Neutral position	Without neutral
Type of pole	3P

##### Electric current

Rated current	80 A
Breaking capacity 400 V AC23A	1,354 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	0.96 kA
Acceptable current rating AC21 category A	80 A
Acceptable current rating AC21 category B	80 A
Acceptable current rating AC22 category A	80 A
Acceptable current rating AC22 category B	80 A
Rated short-circuit making capacity I <sub>cm</sub> under 415 V AC according to IEC 60947-3	1.35 kA
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	0.96 kA

##### Installation, mounting

Nominal tightening torque	3.60 - 3.60 Nm
Type of bottom connection for modular devices	Screw terminal

##### Voltage

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	440 V
Rated impulse withstand voltage U <sub>imp</sub>	6,000 V

##### Capacity

Number of modules	3
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Dimensions

Height	83 mm
Width	52.50 mm

Depth

68 mm

### Equipment

Number of NO contacts	3
Number of NC contacts	0

### Use conditions

Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C

### Connection

Cross-section flexible conductor	6 - 35 mm <sup>2</sup>
Cross-section rigid conductor	6 - 50 mm <sup>2</sup>

### Endurance

Number of mechanical operations	40,000
Electrical durability at nominal load in AC21 in operating cycles	2,500
Electrical durability at nominal load in AC22 in operating cycles	2,500

### Power

Total power loss under IN	8.10 W
Power loss per pole at In	2.70 W

### Connectivity

Down connection alignment for modular devices	Aligned terminal
Top connection alignment for modular devices	Aligned terminal