



WMSS82-USBAC



Double Pole Switched Socket 2 Gang Complete With Twin USB A+C Ports

Technical characteristics

Electric current

Rated current 13 A

Frequency

Frequency 50 - 60 Hz

Safety

Ingress Protection (IP) class IP20

Dimensions

Built-in depth flush-mounted boxes 25 mm

Height 86 mm

Width 146 mm

Depth 19 mm

Materials

Surface finish Glossy

Material Urea formaldehyde

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 0

Texts

Imprint With imprint

Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection
