



SM250

### Analogue ammeter 0-250A indirect reading

#### Technical characteristics

##### Architecture

Fixing mode	Din-Rail
-------------	----------

##### Voltage

Rated insulation voltage	2000 V
--------------------------	--------

##### Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

##### Power

Power consumed	1.1 VA
----------------	--------

Total power loss under IN	1.1 W
---------------------------	-------

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------