



WRCC50NBSB

### 45A Cooker Control Unit Brushed Steel Black Insert

#### Technical characteristics

##### Architecture

Fixing mode flush-mounting

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 45 A

##### Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

##### Cover, door

Cover Full cover plate

##### Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

##### Connection

Type of connection Screw connection

##### Safety

Protection index IP IP20

Protection to protect downstream loads

##### Use conditions

Insert insert, black