



SPA001N

Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV

Technical characteristics

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	100 kA
--	--------

Dimensions

Depth of installed product	52.3 mm
----------------------------	---------

Height of installed product	46.4 mm
-----------------------------	---------

Width of installed product	35.5 mm
----------------------------	---------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------